

Glass bottles pharma veral



Below, you can find the product information of our **standard bottles**. Other variations available on request.

Our reference	Capacity (ml)	Quantity per tray	Quantity per pallet	Height (mm)	Diameter (mm)	Opening product	Weight (g)	Colour	Material
FLVS20413	250	51	1428	133	65	ROPP28	160	Amber	Glass
FLVS20421	300	36	1296	136,5	71,5	ROPP28	185	Amber	Glass
FLVS20443	500	33	660	161	82	ROPP28	285	Amber	Glass
FLVS20458	1000	14	420	206,2	100,6	ROPP28	450	Amber	Glass

Below, you can find the product information of our **standard caps**. We can deliver the same quantity of caps as bottles.

Our reference	Info cap	Quantity per box	Quantity per pallet	Height (mm)	Diameter (mm)	Weight (g)	Colour
293F00707	ROPP28 + IHS* liner	2000	40000	24	32,5	4,3	White
293F00719	ROPP28 + PE foam liner	2000	40000	24	32,5	4	Green
293F00828	ROPP28 + PE foam liner	2000	40000	24	32,5	4	Black
293F00904	ROPP28 + PE plug	3000	60000	24	32,5	4,7	White
293F00707	ROPP28 + IHS* liner	2000	40000	24	32,5	4,3	White
273F00740	ROPP28 child friendly + EPE/ALU liner	1500	30000	29,2	35	8,3	White

**IHS = Induction Heat Seal = Lids with an Induction Heat Seal (IHS) liner are specially designed to show that a jar is unopened. The caps have an adhesive layer on the inside. When the lid encounters an induction field, the layer of aluminium or foil is heated and melts at the cap opening, giving the packaging an extra layer of protection when the cap is removed. Induction seal caps can be applied with a sealing machine.*